# **Product datasheet**

Specifications





## Ø 45 mm tower light - steady clear - IP40

XVDLS37

() Discontinued on: 1 Nov 2020

① Discontinued

### Main

Range Of Product	Harmony XVD Optimum
Product Or Component Type	Complete miniature beacon
Beacon Or Indicator Bank Unit Type	Base unit direct fixing Illuminated unit
Signalling Type	Steady
Mounting Diameter	45 mm
Component Name	XVDLS
Material	Glass reinforced polyamide: base unit Polycarbonate: illuminated unit
Light Source	Bulb not included, clear
Bulb Type	Incandescent with BA 15d base
[Us] Rated Supply Voltage	<= 230 V
Maximum Power Dissipation In W	5 W

pation In W imum Power Di

## Complementary

· · · · · · · · · · · · · · · · · ·	
Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm <sup>2</sup> with cable end
Cable Entry	1 entry tapped for Pg 7
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1
Cad Overall Width	45 mm
Cad Overall Height	104 mm
Cad Overall Depth	45 mm
Terminals Description Iso N°1	(GND)GROUND (COM-1)PW
Net Weight	0.08 kg

## **Environment**

Product Certifications	CSA UL
Standards	EN/IEC 60947-5-1
Protective Treatment	тс
Ambient Air Temperature For Operation	-2570 °C

Ambient Air Temperature For Storage	-4070 °C
Electrical Shock Protection Class	Class II conforming to IEC 60536
Ip Degree Of Protection	IP40 conforming to IEC 60529

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**


Circularity Profile	No need of specific recycling operations
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration

## **Product datasheet**

#### **Dimensions Drawings**

#### Illuminated Beacon

#### Dimensions



## Product datasheet

Mounting and Clearance

#### Illuminated Beacon

#### Panel Cut-out for Direct Fixing

