

# Product datasheet

Specifications



Enclosure for interlocked power outlet, Mureva Enclosure, 1x8 mod, 2 open 103x225mm, (W)236mm x (H)460mm, w/o term block

13186

## Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for power outlet
Mounting Plate Description	Without mounting plate

## Complementary

Enclosure Mounting	Surface
9 Mm Pitches	16
Number Of 18 Mm Modules Per Row	8
Total Number Of 18 Mm Modules	8
Number Of Horizontal Rows	1
Electrical Insulation Class	Class II Double insulation
Number Of Openings Of Interface	2
Number Of Plates	1 for 65 x 65 or 75 x 75 power outlets
Provided Equipment	2 wiring strap 1 plate for 65 x 65 or 75 x 75 power outlet
Type Of Front Cover	Transparent
Power Dissipation In W	15 W
[In] Rated Current	63 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	7
Locking Options Description	Optional keylock
Enclosure Material	Housing: self-extinguishing polymer
Net Weight	2 kg
Base Dimension	103 x 225 mm
Width	236 mm
Height	460 mm
Depth	160 mm
Internal Depth	91 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	Door: transparent green Enclosure: light grey (RAL 7035)
--------	---

## Environment

Standards	IEC 60670 EN 62262 IEC 60695-2-1 IEC 61439-3 EN 50262
Fire Resistance	650 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...40 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	47.000 cm
Package 1 Width	25.600 cm
Package 1 Length	16.800 cm
Package 1 Weight	1.867 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	42
Package 2 Height	80.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	90.414 kg

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Lower Impact Materials   Transparency   RoHS/REACH

Resource performance

✓

Minimum Percentage Of Recycled Plastic Content

25

Well-being performance

✓

Rohs Exemption Information

Yes

✓

Halogen Free Product

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations