Product datasheet

Specification





Miniature circuit breaker (MCB), Acti9 iK60N, 2P, 10A, C curve, 6000A (IEC/EN 60898-1)

A9K27210

Main

Device Application	Distribution
Range	Acti9
Product Name	Acti9 iK60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	iK60N
Poles Description	2P
Number Of Protected Poles	2
[In] Rated Current	10 A at 30 °C
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	С
Breaking Capacity	6000 A Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1
Suitability For Isolation	Yes conforming to EN/IEC 60898-1
Standards	EN/IEC 60898-1
Product Certifications	SNI

Complementary

Network Frequency	50/60 Hz
Magnetic Tripping Limit	510 x ln
[Ics] Rated Service Breaking Capacity	6000 A 100 % conforming to EN/IEC 60898-1 - 230 V AC 50/60 Hz
Limitation Class	3 conforming to EN/IEC 60898-1
[Ui] Rated Insulation Voltage	440 V AC 50/60 Hz conforming to EN/IEC 60898-1
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60898-1
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	4
Height	85 mm
Width	36 mm
Depth	78.5 mm

Net Weight	200 g	
Colour	White	
Mechanical Durability	20000 cycles	
Electrical Durability	10000 cycles	
Locking Options Description	Padlocking device	
Connections - Terminals	Tunnel type terminal (top or bottom) 125 mm² rigid Tunnel type terminal (top or bottom) 116 mm² flexible	
Wire Stripping Length	14 mm for top or bottom connection	
Tightening Torque	2 N.m top or bottom	
Earth-Leakage Protection	Without	

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Pollution Degree	2 conforming to EN/IEC 60898-1
Overvoltage Category	III
Ambient Air Temperature For Operation	-2560 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	9.5 cm
Package 1 Length	3.5 cm
Package 1 Weight	196 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	6
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	1215 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	66
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	14080 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations