Product datasheet

Specifications





Miniature circuit breaker (MCB), Acti9 C60PV-DC, 2P, 16A, B curve, 1.5kA (IEC/EN 60947-2)

A9N61651

Main

mann	
Range Of Product	C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60PV-DC
Poles Description	2P
Number Of Protected Poles	2
Network Type	DC
Curve Code	В
Utilisation Category	Category A conforming to EN/IEC 60947-2
Suitability For Isolation	Yes conforming to EN/IEC 60947-2

Complementary

oompicinentary	
[In] Rated Current	16 A
Voltage Drop	648 mV 40.5 mOhm 10.4 W 16 A
[Ue] Rated Operational Voltage	800 V DC
Magnetic Tripping Limit	5.5 x ln
Breaking Capacity	3 kA lcu at 650 V DC 1.5 kA lcu at 800 V DC
[Ics] Rated Service Breaking Capacity	1.5 kA 100 % - 800 V DC 3 kA 100 % - 650 V DC
[Ui] Rated Insulation Voltage	1000 V DC
[Uimp] Rated Impulse Withstand Voltage	6 kV
Polarity Sensitivity	No (can protect against bi-directional current)
Contact Position Indicator	Yes
Control Type	Toggle
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	8
Height	132.7 mm
Width	72 mm
Depth	77.4 mm
Net Weight	0.545 kg
Colour	White

Mechanical Durability	20000 cycles	
Electrical Durability	1500 cycles L/R = 2 ms	
Locking Options Description	Padlocking in OFF position	
Connections - Terminals	Tunnel terminal (downside) 125 mm² rigid Tunnel terminal (downside) 116 mm² flexible Pre-wired cable (upside)	
Wire Stripping Length	14 mm	
Tightening Torque	2.5 N.m	
Market Segment	Residential Small commercial	
Compatibility Code	C60PV-DC	

Environment

Standards	EN/IEC 60947-2
Pollution Degree	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	7.5 cm
Package 1 Length	13.6 cm
Package 1 Weight	524.5 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	30
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	16.498 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	240
Package 3 Height	15 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	2493.92 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations