# **Product datasheet**

Specifications





# Miniature circuit breaker (MCB), Acti9 C60PV-DC, 2P, 5A, C curve, 1.5kA (IEC/EN 60947-2)

A9N61656

#### Main

in an i		
Range Of Product	C60	
Product Or Component Type	Miniature circuit-breaker	
Device Short Name	C60PV-DC	
Poles Description	2P	
Number Of Protected Poles	2	
Network Type	DC	
Curve Code	C	
Utilisation Category	Category A conforming to EN/IEC 60947-2	
Suitability For Isolation	Yes conforming to EN/IEC 60947-2	

### Complementary

complementary	
[In] Rated Current	5 A
Voltage Drop	2000 mV 400 mOhm 10 W 5 A
[Ue] Rated Operational Voltage	800 V DC
Magnetic Tripping Limit	8.5 x ln
Breaking Capacity	3 kA lcu at 650 V DC 1.5 kA lcu at 800 V DC
[Ics] Rated Service Breaking Capacity	1.5 kA 100 % - 800 V DC 3 kA 100 % - 650 V DC
[Ui] Rated Insulation Voltage	1000 V DC
[Uimp] Rated Impulse Withstand Voltage	6 KV
Polarity Sensitivity	No (can protect against bi-directional current)
Contact Position Indicator	Yes
Control Type	Toggle
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	8
Height	132.7 mm
Width	72 mm
Depth	77.4 mm
Net Weight	0.545 kg
Colour	White

Mechanical Durability	20000 cycles	
Electrical Durability	1500 cycles L/R = 2 ms	
Locking Options Description	Padlocking in OFF position	
Connections - Terminals	Tunnel terminal (downside) 125 mm² rigid Tunnel terminal (downside) 116 mm² flexible Pre-wired cable (upside)	
Wire Stripping Length	14 mm	
Tightening Torque	2.5 N.m	
Market Segment	Residential Small commercial	
Compatibility Code	C60PV-DC	

#### Environment

Standards	EN/IEC 60947-2
Pollution Degree	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	7.5 cm
Package 1 Length	13.6 cm
Package 1 Weight	572 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	30
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	17.017 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	240
Package 3 Height	15 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	2493.92 kg

### **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations