Product datasheet





switch disconnector iSW - 3P - 40 A - 415 V

A9S65340

Main

| ******* | | |
|---------------------------|------------------------|--|
| Range | Acti9 | |
| Product Name | Acti9 iSW | |
| Product Or Component Type | pe Switch disconnector | |
| Device Short Name | iSW | |
| Device Application | Control Isolation | |
| Poles Description | 3P | |
| Utilisation Category | AC-22A | |
| Suitability For Isolation | Yes | |

Complementary

| [le] Rated Operational Current | 40 A at 415 V AC 50/60 Hz | |
|---|--------------------------------|--|
| [Ue] Rated Operational Voltage | 415 V AC 50/60 Hz | |
| [Icm] Rated Short-Circuit Making Capacity | 5 kA switch-disconnector alone | |
| [Icw] Rated Short-Time Withstand Current | d 1260 A | |
| [Ui] Rated Insulation Voltage | 500 V AC 50/60 Hz | |
| [Uimp] Rated Impulse Withstand Voltage | 6 kV | |
| Control Type | Toggle | |
| Local Signalling | ON/OFF indication | |
| Contact Position Indicator | Yes | |
| Mounting Mode | Fixed | |
| Mounting Support | DIN rail | |
| Comb Busbar And Distribution Block Compatibility | Top or bottom: YES | |
| 9 Mm Pitches | 6 | |
| Height | 85 mm | |
| Width | 54 mm | |
| Depth | 73 mm | |
| Colour | White | |
| Mechanical Durability | 20000 cycles | |
| Electrical Durability | 15000 cycles | |

| Connections - Terminals | Tunnel type terminals (top or bottom) - $<= 1 \times 50 \text{ mm}^2 - \text{rigid}$ Tunnel type terminals (top or bottom) - $<= 1 \times 35 \text{ mm}^2 - \text{flexible}$ Tunnel type terminals (top or bottom) - $<= 1 \times 35 \text{ mm}^2 - \text{flexible}$ with ferrule |
|-------------------------|---|
| Wire Stripping Length | 14 mm |
| Tightening Torque | 3.5 N.m |

Environment

| Standards | EN 60947-3 IEC 60947-3 |
|---------------------------------------|---------------------------|
| Ip Degree Of Protection | IP20 |
| Pollution Degree | 3 |
| Tropicalisation | 2 |
| Relative Humidity | 95 % at 55 °C |
| Ambient Air Temperature For Operation | -2560 °C |
| Ambient Air Temperature For Storage | -4085 °C |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.500 cm |
| Package 1 Width | 7.500 cm |
| Package 1 Length | 9.500 cm |
| Package 1 Weight | 250.500 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 4 |
| Package 2 Height | 8.500 cm |
| Package 2 Width | 10.000 cm |
| Package 2 Length | 22.000 cm |
| Package 2 Weight | 1.054 kg |
| Unit Type Of Package 3 | S03 |
| Number Of Units In Package 3 | 44 |
| Package 3 Height | 30.000 cm |
| Package 3 Width | 30.000 cm |
| Package 3 Length | 40.000 cm |
| Package 3 Weight | 12.084 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc | |
|----------|------------------------------------|-----|
| ⊘ | Toxic Heavy Metal Free | |
| ⊘ | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |
| Ø | Halogen Free Plastic Parts Product | |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant |
| | EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |