# **Product datasheet**

Specifications





# switch disconnector iSW - 3P - 100 A - 415 V

A9S65391

#### Main

Range	Acti9	
Product Name	Acti9 iSW	
Product Or Component Type	Switch disconnector	
Device Short Name	iSW	
Device Application	Control Isolation	
Poles Description	3P	
Utilisation Category	AC-22A	
Suitability For Isolation	Yes	

### Complementary

[le] Rated Operational Current	100 A at 415 V AC 50/60 Hz	
[Ue] Rated Operational Voltage	415 V AC 50/60 Hz	
[Icm] Rated Short-Circuit Making Capacity	5 kA switch-disconnector alone	
[Icw] Rated Short-Time Withstand Current	d 1500 A	
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz	
[Uimp] Rated Impulse Withstand Voltage	nd 6 kV	
Control Type	Toggle	
Local Signalling	ON/OFF indication	
Contact Position Indicator	Yes	
Mounting Mode	Fixed	
Mounting Support	DIN rail	
Comb Busbar And Distribution Block Compatibility	Top or bottom: YES	
9 Mm Pitches	6	
Height	85 mm	
Width	54 mm	
Depth	73 mm	
Colour	White	
Mechanical Durability	20000 cycles	
Electrical Durability	10000 cycles	

Connections - Terminals	Tunnel type terminals (top or bottom) - $<= 1 \times 50 \text{ mm}^2 - \text{rigid}$ Tunnel type terminals (top or bottom) - $<= 1 \times 35 \text{ mm}^2 - \text{flexible}$ Tunnel type terminals (top or bottom) - $<= 1 \times 35 \text{ mm}^2 - \text{flexible}$ with ferrule
Wire Stripping Length	14 mm
Tightening Torque	3.5 N.m

#### **Environment**

Standards	IEC 60947-3 EN 60947-3
Ip Degree Of Protection	IP20
Pollution Degree	3
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-2560 °C
Ambient Air Temperature For Storage	-4085 °C

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	7.500 cm
Package 1 Length	9.500 cm
Package 1 Weight	250.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	4
Package 2 Height	8.500 cm
Package 2 Width	10.000 cm
Package 2 Length	22.000 cm
Package 2 Weight	1.053 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	44
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	11.987 kg

#### **Contractual warranty**

Warranty 18 months



Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Plastic Parts Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations