



# Power Cord Kit (6 ea), Locking, C13 TO C14, 0.6m, Red

AP8702S-WWX340

#### **Overview**

Lead Time Usually in Stock

#### Main

Input Connection Type	IEC 60320 C14
Cable Length	0.61 m
Number Of Cables	6

### **Physical**

Colour	Red
Height	24 cm
Width	7 cm
Depth	4 cm
Net Weight	0.7 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

# Input

Max Line Current	10 A
Input Current Limits	10 A

# Output

Max Current Draw	10 A
Number Of Power Socket Outlets	1 IEC 60320 C13
Power Cable Length	0.61 m

#### Conformance

Product Certifications	CCC	
	PSE	
	VDF	

#### **Environmental**

Ambient Air Temperature For Operation	070 °C
Relative Humidity	2080 %
Operating Altitude	010000 ft

Ambient Air Temperature For Storage	-2575 °C
Storage Relative Humidity	2080 %
Storage Altitude	0.00 15240.00 m

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24 cm
Package 1 Width	4 cm
Package 1 Length	7 cm
Package 1 Weight	0.7 kg

# **Contractual warranty**

Warranty 2 years repair or replace



Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Take-back Transparency RoHS/REACh

#### Resource performance

Take-Back Program Available

#### Well-being performance

Toxic Heavy Metal Free



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile