





Power Cord Kit (6 ea), Locking, C13 to C14, 1.2m, Red

AP8704S-WWX340

Overview

Lead Time Usually in Stock

Main

Input Connection Type	IEC 60320 C14
Cable Length	1.22 m
Number Of Cables	6

Physical

Colour	Red
Height	24 cm
Width	7 cm
Depth	4.5 cm
Net Weight	1.01 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Max Line Current	10 A
Input Current Limits	10 A

Output

Max Current Draw	10 A
Number Of Power Socket Outlets	1 IEC 60320 C13
Power Cable Length	1.22 m

Conformance

Product Certifications	CCC		
	PSE		
	VDE		

Environmental

Ambient Air Temperature For Operation	070 °C
Relative Humidity	2080 %
Operating Altitude	010000 ft

Ambient Air Temperature For Storage	-2575 °C
Storage Relative Humidity	2080 %
Storage Altitude	0.00 15240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24 cm
Package 1 Width	4.5 cm
Package 1 Length	7 cm
Package 1 Weight	1.01 kg

Contractual warranty

Warranty 2 years repair or replace



Green Premium TM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation REACh Declaration Eu Rohs Directive Compliant **EU RoHS Declaration Environmental Disclosure Product Environmental Profile Circularity Profile** End of Life Information