

Product datasheet

Specifications



ZENcelo -16AX 1G 1 Way Full-Flat Switch with Ondicat-w/Blister-Silver Bronze

E8431_1_SZ

Main

Range	ZENcelo
Product or component type	Switch
Load type	Incandescent lamp Fluorescent lamp Resistive Inductive
Colour tint	Silver bronze
Cover frame colour tint	Silver bronze

Complementary

Device mounting	Flush Surface
Switch function	1-way
Rated current	20 A at 250 V AC 50 Hz
Local signalling	Mechanical indicator, neon (amber)
Number of gangs	1 gang
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround
Connections - terminals	Brass rod terminals
Width	87 mm
Height	87 mm
Depth	31 mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	SS 227-1 GB 16915.1 EN 60669-1 MS IEC 60669-1 IEC 60669-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	98.375 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	787 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	7870 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)