

Product datasheet

Specifications



16 A X/20 A 2 gang 2wfull - flat switch White

E8432_2_WE

Main

Range	ZENcelo
Product or component type	Switch
Device application	Control
Load type	Inductive Incandescent lamp Fluorescent lamp Resistive

Complementary

Device mounting	Surface Flush
Switch function	2-way
Rated current	20 A/16 AX at 250 V AC 50 Hz
Number of gangs	2 gangs
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	131.26 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)