

Product datasheet

Specifications



16 A X/20 A 3 gang 2 w full - flat switch White

E8433_2_WE

Main

Range	ZENcelo
Product or component type	Switch
Device application	Control
Load type	Resistive Inductive Fluorescent lamp Incandescent lamp

Complementary

Device mounting	Surface Flush
Switch function	2-way
Rated current	20 A/16 AX at 250 V AC 50 Hz
Number of gangs	3 gangs
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	132.47 g
Unit Type of Package 2	S04
Number of Units in Package 2	80
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	10.678 kg
Unit Type of Package 3	P12

Number of Units in Package 3	1600
Package 3 Height	125 cm
Package 3 Width	105 cm
Package 3 Length	80 cm
Package 3 Weight	215.16 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)