

# Product datasheet

Specifications



## Vivace 20A 250V 2gang Double Pole Switch with Neon and Earth,Aluminium Silver

KB32D20NE\_AS

 **Discontinued on:** Jun 30, 2023 AD

 **Discontinued**

### Main

Range	Vivace
Product Or Component Type	Switch
Device Short Name	KB32
Device Application	Control
Switch Function	Double 1-way with earth

### Complementary

Device Presentation	Complete mechanism
Actuator	Rocker
Pilot Light	Neon indicator lamp
Number Of Gangs	2 gangs
Colour Tint	Aluminium silver
Material	Polycarbonate: grid plate Polycarbonate: surround Nylon: base
Projecting Depth	8 mm
Device Mounting	Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Fixing Center	60.3 mm
Embedding Depth	35 mm
Rated Current	20 A at 250 V AC, inductive 20 A at 250 V AC, resistive
[Ue] Rated Operational Voltage	250 V AC
Network Frequency	50 Hz
Contacts Material	Brass and phosphor bronze
Connections - Terminals	pillar terminal
Terminal Identifier	N1 L2 L1 N2
Tightening Torque	0.4 N.m
Clamping Connection Capacity	<= 2.5 mm²

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	86 mm
Height	86 mm

## Environment

Standards	SS 227 MS IEC 60669-1 IEC 60669-1
Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	102 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	888 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	8490 g

# Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information