# **Product datasheet**

Specifications





# Data socket, Vivace, cat 5E, with shutter, 2 gang, white

KB32RJ5E

#### Main

Range	Vivace
Device Short Name	KB32
Product Or Component Type	Data socket
Device Application	Communication
Cover Type	Shutter
Device Presentation	Complete mechanism
Colour Tint	White

### Complementary

Connector Type	M-110 keystone RJ45 connector	
Communication Network Category	5e	
Number Of Gangs	2 gangs	
Tightening Torque	0.4 N.m	
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base	
Device Mounting	Flush	
Mounting Support	Wall mounted	
Fixing Mode	By screw M3.5	
Fixing Center	60.3 mm	
Width	87 mm	
Height	87 mm	
Projecting Depth	8 mm	
Embedding Depth	35 mm	
Data Socket Type	RJ45 Cat.5e	
Main Colour Tint	White	

#### **Environment**

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use
Standards	FCC

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	5 cm
Package 1 Length	8.6 cm
Package 1 Weight	100.6 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	875 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	8300 g

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations