Product datasheet

Specification





Enclosure, Resi9 MP, surface mounting, 1 row of 8 modules, IP40, smoked door, 1 earth + 1 neutral terminal blocks

MIP12108S

Main

Range	Resi9
Product Name	Resi9 MP
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	8
Nb Of Horizontal Rows	1
Type Of Door	Smoked
Width	196 mm outside:
Height	198 mm outside:
Depth	101.5 mm outside:

Complementary

<u> </u>	
Enclosure Mounting	Surface
9 Mm Pitches	16
Total Number Of 18 Mm Modules	8
[In] Rated Current	63 A
Type Of Rail	35 mm asymmetrical rail
Mounting Plate Description	Without mounting plate
Cable Entry	1 trunking flange 1 bare flange
Terminal Block Function	Earth / neutral
Number Of Terminal Blocks	1 earth (screwed) with 8 outgoers 1 neutral (screwed) with 8 outgoers
Distribution Block Outgoers	1 x 16 mm² for earth 1 x 16 mm² for neutral 3 x 6 mm² for earth 3 x 6 mm² for neutral 4 x 10 mm² for earth 4 x 10 mm² for neutral
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Internal Depth	80 mm
Colour	Front face: white (RAL 9003) Door: smoked (RAL 9003)
Market Segment	Small commercial Residential

Environment

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality Labels	IMQ
Fire Resistance	Door: 650 °C Back part: 650 °C Front face: 650 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-2560 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.400 cm
Package 1 Width	20.000 cm
Package 1 Length	22.900 cm
Package 1 Weight	689.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	36.000 cm
Package 2 Width	41.100 cm
Package 2 Length	54.100 cm
Package 2 Weight	7.242 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	160
Package 3 Height	120.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	127.872 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations