# **Product datasheet**

Specification





Enclosure, Resi9 MP, surface mounting, 1 row of 18 modules, IP40, white door, 1 earth + 1 neutral terminal blocks

MIP12118

#### Main

Range	Resi9
Product Name	Resi9 MP
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	18
Nb Of Horizontal Rows	1
Type Of Door	Plain
Width	Outside: 376 mm
Height	Outside: 228 mm
Depth	101.5 mm outside:

### Complementary

<b>Enclosure Mounting</b>	Surface
9 Mm Pitches	36
Total Number Of 18 Mm Modules	18
[In] Rated Current	63 A
Type Of Rail	35 mm asymmetrical rail
Mounting Plate Description	Without mounting plate
Cable Entry	1 bare flange 1 trunking flange
Terminal Block Function	Earth / neutral
Number Of Terminal Blocks	1 earth (screwed) with 16 outgoers 1 neutral (screwed) with 16 outgoers
Distribution Block Outgoers	2 x 16 mm² for earth 2 x 16 mm² for neutral 6 x 6 mm² for earth 6 x 6 mm² for neutral 8 x 10 mm² for earth 8 x 10 mm² for neutral
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Internal Depth	80 mm
Colour	Door: white (RAL 9003) Front face: white (RAL 9003)
Market Segment	Small commercial Residential

#### **Environment**

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality Labels	IMQ
Fire Resistance	Door: 650 °C Back part: 650 °C Front face: 650 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-2560 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.000 cm
Package 1 Width	23.000 cm
Package 1 Length	37.500 cm
Package 1 Weight	1.105 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	5
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	6.365 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	80
Package 3 Height	122.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	113.840 kg

# **Contractual warranty**

Warranty 18 months



Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

# Well-being performance



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations