



socket, Harmony Electromechanical Relays, for RXM2LB RXM4LB relays,7A, screw clamp socket, mixed contact terminal

RXZE1M4C

Main

| Range Of Product | Harmony Electromechanical Relays | |
|--|---|--|
| Device Short Name | RXZ | |
| Product Or Component Type | Socket | |
| Product Compatibility | Plug-in relay RXM with 2 C/O contact Plug-in relay RXM with 4 C/O contact | |
| Contacts Type And Composition | 4 C/O | |
| [Ith] Conventional Free Air Thermal Current | 7 A | |

Complementary

| [Ue] Rated Operational Voltage | 250 V AC conforming to IEC | |
|--|---|--|
| Contact Terminal Arrangement | Mixed | |
| Connections - Terminals | Screw clamp terminals, 1 x 0.21 x 1.0 mm² (AWG 24AWG 17) flexible with cable end Screw clamp terminals, 2 x 0.22 x 1.0 mm² (AWG 24AWG 17) flexible with cable | |
| | end Screw clamp terminals, 1 x 0.51 x 1.5 mm² (AWG 20AWG 16) solid without cable end | |
| | Screw clamp terminals, 2 x 0.52 x 1.5 mm 2 (AWG 20AWG 16) solid without cable end | |
| Tightening Torque | < 0.8 N.m for M3 screw(s) | |
| Fixing Mode | By screw (panel) Clip-on (35 mm symmetrical DIN rail) | |
| [Uimp] Rated Impulse Withstand Voltage | 4 kV | |
| Overvoltage Category | III | |
| Pollution Degree | 3 | |
| Sale Per Indivisible Quantity | 10 | |
| Width | 29 mm | |
| Net Weight | 0.053 kg | |

Environment

| Dielectric Strength | 2500 V |
|---------------------------------------|-----------|
| Standards | IEC 61984 |
| Marking | CE |
| Ambient Air Temperature For Storage | -5585 °C |
| Ambient Air Temperature For Operation | -4055 °C |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.9 cm |
| Package 1 Width | 3.1 cm |
| Package 1 Length | 7.5 cm |
| Package 1 Weight | 0.052 kg |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 6.8 cm |
| Package 2 Width | 8.0 cm |
| Package 2 Length | 14.9 cm |
| Package 2 Weight | 0.541 kg |
| Unit Type Of Package 3 | S03 |
| Number Of Units In Package 3 | 270 |
| Package 3 Height | 30.0 cm |
| Package 3 Width | 30.0 cm |
| Package 3 Length | 40.0 cm |
| Package 3 Weight | 14.9 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| ② | Toxic Heavy Metal Free | |
| 9 | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |


Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

RXZE1M4C

Dimensions Drawings

Dimensions



RXZE1M4C

Connections and Schema

Wiring Diagram

