# **Product datasheet**

Specification





# socket, Harmony Electromechanical Relays, for RXM2 RXM4 relays, screw connec to rs, mixed contact

RXZE2M114M

## Main

Range Of Product	Harmony Electromechanical Relays Harmony Timer Relays
Device Short Name	RXZ
Product Or Component Type	Socket
Product Compatibility	Plug-in relay RXM with 2 C/O contact Plug-in relay RXM with 4 C/O contact
Contacts Type And Composition	4 C/O
[Ith] Conventional Free Air Thermal Current	10 A

# Complementary

Shape Of Pin	Flat	
[Ue] Rated Operational Voltage	< 250 V	
Contact Terminal Arrangement	Mixed	
Connections - Terminals	Connector, 1 x 0.251 x 2.5 mm² (AWG 22AWG 14) flexible with cable end Connector, 2 x 0.252 x 1 mm² (AWG 22AWG 17) flexible with cable end Connector, 1 x 0.51 x 2.5 mm² (AWG 20AWG 14) solid without cable end Connector, 2 x 0.52 x 1.5 mm² (AWG 20AWG 16) solid without cable end	
Tightening Torque	< 1 N.m for M3 screw(s)	
Fixing Mode	By screw (panel) Clip-on (35 mm symmetrical DIN rail)	
[Uimp] Rated Impulse Withstand Voltage	4 kV	
Overvoltage Category	III	
Pollution Degree	3	
Sale Per Indivisible Quantity	10	
Width	27 mm	
t Weight 0.056 kg		

## **Environment**

Ip Degree Of Protection	IP20 conforming to IEC 60529	
Dielectric Strength	3000 V	
Standards	IEC 61984	
Product Certifications	UL CSA Lloyd's	
Marking	CE	

Ambient Air Temperature For Storage	-4085 °C
Ambient Air Temperature For Operation	-4055 °C

# **Packing Units**

PCE
1
2.686 cm
4.245 cm
7.918 cm
0.054 kg
BB1
10
7.5 cm
8.8 cm
14.0 cm
0.561 kg
S02
120
15.0 cm
30.0 cm
40.0 cm
7.281 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance


<b>Ø</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

#### **Dimensions Drawings**

#### **Dimensions**



- (1) Relays(2) Protection module
- (3) Maintaining clamp
- (4) 2 elongated holes Ø 3.5 mm x 6.5 mm / Ø 0.13 in. x 0.25 in.

Connections and Schema

## Wiring Diagram

