Product datasheet

Specifications





Kavacha - 63A - 440V - Surface Mount Double Pole Isolating Switch - IP66

WHD63_GY

Main

Range	Kavacha
Product Or Component Type	Isolating switch
Device Short Name	W
Device Application	Control

Complementary

[le] Rated Operational Current	63 A at 440 V AC-22A
Poles Description	2P
Motor Rating	M160
Width	82 mm
Height	170 mm
Depth	90 mm

Environment

Ip Degree Of Protection	IP66
Standards	IEC 60947-3
Environmental Characteristic	Weatherproof

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.3 cm
Package 1 Width	9.0 cm
Package 1 Length	8.3 cm
Package 1 Weight	1.6 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations