Product datasheet

Specification





Monolithic pilot light, Easy Harmony XA2, plastic, white, 22mm, integral LED, screw clamp terminals, 220V DC

XA2EVMD1LC

Main

Range Of Product	Easy Harmony XA2	
Product Or Component Type	Monolithic pilot light	
Device Short Name	XA2	
Mounting Diameter	22.5 mm	
Shape Of Signaling Unit Head	Round	
Cap/Operator Or Lens Colour	ur White	
Light Source	LED	
Bulb Base	Integral LED	
[Us] Rated Supply Voltage	220 V DC	

Complementary

(X1-X2)PL
Fixing hole 22.3 +0.4/0 conforming to IEC 60947-5-1
>= 30 x 40 mm (support panel) metal - thickness: 16 mm >= 30 x 40 mm (support panel) plastic - thickness: 26 mm
Fixing nut beneath head recommended torque: 2.2 N.m (+/- 0.2 N.m)
CCC CE
220 V
Screw clamp terminals, <= 2 x 1.5 mm² with cable end conforming to IEC 60947-1 Screw clamp terminals, 1 x 0.51 x 2.5 mm² without cable end conforming to IEC 60947-1
0.81 N.m conforming to IEC 60947-1
Cross compatible with Philips No 2 screwdriver Slotted compatible with flat Ø 4 mm screwdriver Slotted compatible with flat Ø 5.5 mm screwdriver
400 V (pollution degree 3) conforming to IEC 60947-1
6 kV conforming to IEC 60947-1
Steady
0.81.2 V DC
<= 20 mA
40000 h at rated voltage and 25 °C
29 mm
29 mm

Depth	53 mm
Net Weight	0.02 kg

Environment

Ambient Air Temperature For Storage	-4070 °C	
Ambient Air Temperature For Operation	-2570 °C	
Overvoltage Category	Class I conforming to IEC 536	
Ip Degree Of Protection	IP65 conforming to IEC 60529	
Ik Degree Of Protection	IK05	
Standards	GB 14048.5 IEC 60947-5-1 GB 14048.1 IEC 60947-1 IEC 60529 IEC 50102	
Product Certifications	CE CCC	
Vibration Resistance	nce 5 gn (f= 12500 Hz) conforming to IEC 60068-2-6	
Shock Resistance	30 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	2.9 cm
Package 1 Length	2.9 cm
Package 1 Weight	21.6 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	5.8 cm
Package 2 Width	6.4 cm
Package 2 Length	15.8 cm
Package 2 Weight	300.0 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	160
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	5.8 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


②	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings

Dimensions



e: Calmping thickness:1 to 6 mm/0.04 to 0.24 in.


Product datasheet

XA2EVMD1LC

Mounting and Clearance

Mounting

Diameter of Finished Fixing Holes



- (1) Minimum value.
- (2) 40 mm/1.58 in. for Emergency switching off pushbutton only.
- (3) Standard value: Ø 22.3 (0; + 0.4) mm/Ø 0.88 (0; + 0.02) in.

Connections and Schema

Wiring Diagram



(1) LED