

เอกสารข้อมูลผลิตภัณฑ์

ข้อมูลจำเพาะ



Acti9 iL single indicator light - Blue - 110-230 Vac

A9E18323

Main

Range Of Product	Acti9
Product Name	Acti9 iL
Product Or Component Type	Modular pilot lighth
Device Short Name	iL
[Us] Rated Supply Voltage	110...230 V AC at 50/60 Hz 110...130 V DC

Complementary

Indicator Light	1 LED blue, service life 100000 h of constant lighting efficiency (consumption 0.3 W)
Mounting Mode	Fixed
Mounting Support	Symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	Upside: ProDis
9 Mm Pitches	2
Height	82 mm
Width	18 mm
Depth	69.5 mm
Colour	White (RAL 9003)
Auxiliary Connection Terminal	Tunnel type terminal 1 cable(s) rigid 0.5 mm ² Tunnel type terminal 2 cable(s) rigid 2.5 mm ² Tunnel type terminal 1 cable(s) flexible 0.5 mm ² Tunnel type terminal 2 cable(s) flexible 2.5 mm ² Tunnel type terminal 2 cable(s) flexible with ferrule 2.5 mm ²
Wire Stripping Length	9 mm
Tightening Torque	1 N.m

Environment

Standards	IEC 60947-5-1
Ip Degree Of Protection	IP2 IPxx B
Pollution Degree	3
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-35...70 °C
Ambient Air Temperature For Storage	-40...80 °C

การดูแลรักษา: เอกสารนี้ไม่มีวัตถุประสงค์เพื่อใช้แทน หรือใช้เพื่อกำหนดความเหมาะสม หรือความน่าเชื่อถือของผลิตภัณฑ์เหล่านี้สำหรับการใช้งานเฉพาะทาง

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.800 cm
Package 1 Width	6.600 cm
Package 1 Length	8.700 cm
Package 1 Weight	38.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	7.800 cm
Package 2 Width	9.800 cm
Package 2 Length	23.300 cm
Package 2 Weight	519.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	5.159 kg

Contractual warranty

Warranty	18 months
----------	-----------

ความยั่งยืน

ฉลาก **Green Premium™** เป็นความมุ่งมั่นของSchneider Electric ในการส่งมอบผลิตภัณฑ์ที่มีประสิทธิภาพด้านสิ่งแวดล้อมที่ดีที่สุด Green Premium ให้คำมั่นว่าจะปฏิบัติตามกฎระเบียบล่าสุด ความโปร่งใสต่อผลกระทบด้านสิ่งแวดล้อม รวมถึงผลิตภัณฑ์หมุนเวียนและ CO₂ ต่ำ

คู่มือการประเมินความยั่งยืนของผลิตภัณฑ์เป็นเอกสารวิจัยที่ช่วยชี้แจงมาตรฐานฉลากสิ่งแวดล้อมทั่วโลกและวิธีการตีความการประเมิน

[เรียนรู้เพิ่มเติมเกี่ยวกับ Green Premium >](#)

[แนวทางในการประเมินความยั่งยืนของผลิตภัณฑ์ >](#)



ความโปร่งใส RoHS/REACH

ประสิทธิภาพด้านสุขภาพ

✓ Mercury Free	
✓ Rohs Exemption Information	Yes
✓ Halogen Free Plastic Parts & Cables Product	

ใบรับรองและมาตรฐาน

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations