Product datasheet





FRONT PLATE NSX/CVS 630 **VERTICAL FIXED ROTARY** HANDLE W300 12M

03283

! Discontinued on: 5 Apr 2023

① Discontinued

EAN Code: 3303430032830

Main

Range	Prisma
Range Of Product	Prisma G
•	Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G duct
	Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Installed Device	ComPact: fixed NSX400 without earth leakage protection - control: toggle - vertical installation
	EasyPact: fixed CVS400 without earth leakage protection - control: direct front rotary
	handle - vertical installation
	EasyPact: fixed CVS630 without earth leakage protection - control: direct front rotary handle - vertical installation
	ComPact: fixed NSX400 without earth leakage protection - control: direct front rotary
	handle - vertical installation
	ComPact: plug-in NSX400 without earth leakage protection - control: toggle - vertical installation
	ComPact: fixed NSX400 without earth leakage protection - control: motor mechanism
	- vertical installation
	ComPact: plug-in NSX400 without earth leakage protection - control: direct front
	rotary handle - vertical installation
	ComPact: plug-in NSX400 without earth leakage protection - control: motor
	mechanism - vertical installation ComPact: fixed NSX630 without earth leakage protection - control: toggle - vertical
	installation
	ComPact: fixed NSX630 without earth leakage protection - control: direct front rotary
	handle - vertical installation
	ComPact: plug-in NSX630 without earth leakage protection - control: toggle - vertical
	installation ComPact: fixed NSX630 without earth leakage protection - control: motor mechanism
	- vertical installation
	ComPact: plug-in NSX630 without earth leakage protection - control: direct front
	rotary handle - vertical installation
	ComPact: plug-in NSX630 without earth leakage protection - control: motor
	mechanism - vertical installation
Poles Description	1 x 4P: mounting plate support: NSX400 vertical installation
	1 x 3P: mounting plate support: CVS400 vertical installation
	1 x 4P: mounting plate support: CVS400 vertical installation
	1 x 3P: mounting plate support: CVS630 vertical installation
	1 x 4P: mounting plate support: CVS630 vertical installation 1 x 3P: mounting plate support: NSX400 vertical installation
	1 x 3P: mounting plate support: NSX400 vertical installation
	1 x 4P: mounting plate support: NSX630 vertical installation
Operating Position	Vertical

Complementary

Life Is On Schneider 26 Apr 2024

Enclosure/Cubicle Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle duct - width 400 mm depth 400 mm
Connection Position	Direct connection Front connection
Number Of Vertical Modules [50 Mm]	12
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	600 mm
Width	300 mm
Net Weight	1.24 kg
Quantity Per Set	Set of 1

Functional Unit

- 400 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed toggle vertical 3P 1 front connection 12
- 400 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed toggle vertical 4P 1 front connection 12
- 400~mm 400~mm Prisma P cubicle ComPact NSX400 without fixed direct front rotary handle vertical 3P 1 front connection 12
- 400~mm 400~mm Prisma P cubicle ComPact NSX400 without fixed direct front rotary handle vertical 4P 1 front connection 12
- 400 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed motor mechanism vertical 3P 1 front connection 12
 400 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed motor mechanism
- vertical 4P 1 front connection 12
 400 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in toggle vertical
- 3P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in toggle vertical
- 4P 1 front connection 12 400 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in direct front
- 400 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in direct front rotary handle vertical 3P 1 front connection 12
- 400 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in direct front rotary handle vertical 4P 1 front connection 12
- 400~mm 400~mm Prisma P cubicle ComPact NSX400 without plug-in motor mechanism vertical 3P 1 front connection 12
- 400 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in motor mechanism vertical 4P 1 front connection 12
- 400 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed toggle vertical 3P 1 front connection 12
- 400~mm 400~mm Prisma P cubicle ComPact NSX630 without fixed toggle vertical 4P 1 front connection 12
- 400 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed direct front rotary handle vertical 3P 1 front connection 12
- 400 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed direct front rotary handle vertical 4P 1 front connection 12
- 400~mm 400~mm Prisma P cubicle ComPact NSX630 without fixed motor mechanism vertical 3P 1 front connection 12
- 400~mm 400~mm Prisma P cubicle ComPact NSX630 without fixed motor mechanism vertical 4P 1 front connection 12
- 400 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in toggle vertical 3P 1 front connection 12
- 400 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in toggle vertical 4P 1 front connection 12
- 400 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in direct front rotary handle vertical 3P 1 front connection 12
- 400 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in direct front rotary handle vertical 4P 1 front connection 12
- 400 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in motor mechanism vertical 3P 1 front connection 12
- 400 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in motor mechanism vertical 4P 1 front connection 12
- 300 mm Prisma G floor-standing duct EasyPact CVS400 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 $\,$
- $300~\rm mm$ Prisma G wall-mounted duct EasyPact CVS400 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12
- 300 mm Prisma G floor-standing duct EasyPact CVS400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 $\,$
- 300 mm Prisma G wall-mounted duct EasyPact CVS400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12
- 300 mm Prisma G floor-standing duct EasyPact CVS630 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12
- 300 mm Prisma G wall-mounted duct EasyPact CVS630 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12
- 300 mm Prisma G floor-standing duct EasyPact CVS630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12
- 300 mm Prisma G wall-mounted duct EasyPact CVS630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12
- 300 mm Prisma G floor-standing duct ComPact NSX400 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12
- 300 mm Prisma G wall-mounted duct ComPact NSX400 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12
- 300 mm Prisma G floor-standing duct ComPact NSX400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12
- 300 mm Prisma G wall-mounted duct ComPact NSX400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 300 mm Prisma G floor-standing duct ComPact NSX630 without fixed direct front
- rotary handle vertical 3P 1 direct with long terminal shield 12 300 mm Prisma G wall-mounted duct ComPact NSX630 without fixed direct front
- rotary handle vertical 3P 1 direct with long terminal shield 12 300 mm Prisma G floor-standing duct ComPact NSX630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12
- 300 mm Prisma G wall-mounted duct ComPact NSX630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	26.000 cm
Package 1 Length	61.000 cm
Package 1 Weight	1.200 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	17.000 cm
Package 2 Width	54.000 cm
Package 2 Length	82.000 cm
Package 2 Weight	13.250 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	40
Package 3 Height	49.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	54.800 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile