Product datasheet

Specifications





mini Kaedra - for modular device -1 openings - 3 modules

Local distributor code: 393100138

13975

EAN Code: 3303430139751

Main

| Range | Mureva |
|----------------------------|-----------------------------------|
| Product Name | Mureva Enclosure |
| Product Or Component Type | Weatherproof enclosure |
| Enclosure Type | Mini enclosure for modular device |
| Mounting Plate Description | Slotted |

Complementary

| complementary | |
|------------------------------------|---|
| Enclosure Mounting | Surface |
| 9 Mm Pitches | 6 |
| Number Of 18 Mm Modules Per Row | 3 |
| Total Number Of 18 Mm Modules | 3 |
| Number Of Horizontal Rows | 1 |
| Electrical Insulation Class | Double insulation Class II |
| Provided Equipment | 1 marking kit |
| Type Of Front Cover | Transparent |
| [In] Rated Current | 63 A |
| Type Of Rail | DIN |
| Number Of Pre-Cutouts Pg Iso | 1 |
| Locking Options Description | Optional keylock |
| Enclosure Material | Self-extinguishing polymer |
| Width | 80 mm |
| Height | 150 mm |
| Depth | 98 mm |
| Internal Depth | 56 mm |
| Colour | Door: transparent green Enclosure: light grey (RAL 7035) |

Environment

| Standards | IEC 61439-3 IEC 60670 IEC 60695-2-1 EN 50262 |
|-----------------|---|
| Fire Resistance | 650 °C conforming to IEC 60695-2-1 |

| Ip Degree Of Protection | 35 conforming to IEC 60529 | |
|--|---|--|
| Ik Degree Of Protection | IK09 conforming to EN 50102 | |
| Environmental Characteristics (Uv) | UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013 | |
| Overvoltage Category | 11 | |
| Ambient Air Temperature For Operation | -2560 °C | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 8.000 cm |
| Package 1 Width | 15.000 cm |
| Package 1 Length | 10.000 cm |
| Package 1 Weight | 255.000 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 20 |
| Package 2 Height | 22.500 cm |
| Package 2 Width | 34.500 cm |
| Package 2 Length | 40.000 cm |
| Package 2 Weight | 5.412 kg |
| Unit Type Of Package 3 | P12 |
| Number Of Units In Package 3 | 480 |
| Package 3 Height | 80.000 cm |
| Package 3 Width | 80.000 cm |
| Package 3 Length | 120.000 cm |
| Package 3 Weight | 142.200 kg |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Lower Impact Materials Transparency RoHS/REACh

Resource performance

Minimum Percentage Of Recycled 24 Plastic Content

Well-being performance

| Rohs Exemption Information | Yes |
|----------------------------|-----|
| Halogen Free Product | |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |