



# control unit Micrologic 5.0, for Masterpact NT/NW, LSI protections

33070

EAN Code: 3303430330707

#### Main

Wall	
Product Or Component Type	Control unit
Trip Unit Name	MicroLogic 5.0
Trip Unit Technology	Electronic
Range Compatibility	MasterPact NT
	MasterPact NW
	Compact NS
	Masterpact MT
	PowerPact P-Frame
	PowerPact R-Frame
Device Application	Distribution
Number Of Poles	4P
	3P
Protected Poles Description	3t
	3t + N/2
	4t
Trip Unit Protection Functions	Selective protection
Protection Type	for short time short-circuit protection
	for overload protection (long time)
	for instantaneous short-circuit protection
Trip Unit Rating	630 A at 50 °C
	800 A at 50 °C
	1000 A at 50 °C
	1250 A at 50 °C
	1600 A at 50 °C
	2000 A at 50 °C
	2500 A at 50 °C
	3200 A at 50 °C
	4000 A at 50 °C
	5000 A at 50 °C
	6300 A at 50 °C
Network Type	AC
Network Frequency	50/60 Hz
Circuit Breaker Mounting Mode	Fixed
	Drawout

### Complementary

Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.41 x ln
Long-Time Protection Delay Adjustment Type Tr	Adjustable 9 settings
[Tr] Long-Time Protection Delay Adjustment Range	0.716.6 s at 7.2 x lr 0.524 s at 6 x lr 12.5600 s at 1.5 x lr

Thermal Memory	20 mn
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable 9 settings
[Isd] Short-Time Protection Pick- Up Adjustment Range	1.510 x lr
Short-Time Protection Delay Adjustment Type Tsd	Adjustable
[Tsd] Short-Time Protection Delay Adjustment Range	00.4 s l²t=off 0.10.4 s l²t=on
Instantaneous Protection Pick-Up Adjustment Type Ii	Adjustable 9 settings
[li] Instantaneous Protection Pick- Up Adjustment Range	215 x ln Off
Earth-Leakage Protection	Without
Zone Selective Interlocking Zsi	Without
Local Signalling	3 LEDs (red) for electrical fault 1 LED (red) for internal error

### **Environment**

Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22 cm
Package 1 Width	8 cm
Package 1 Length	7 cm
Package 1 Weight	160 g

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information