



Main

Product name	ComPact NS
Device short name	Compact NS1600 NA
Product or component type	Switch disconnecter
Device application	Distribution
Offer type	C4
Poles description	4P
Network type	AC
Performance level	NA
Suitability for isolation	Yes conforming to IEC 60947-3

Complementary

Network frequency	50/60 Hz
Control type	Toggle
Mounting mode	Fixed
Upside connection	Front
Downside connection	Front
[Ie] rated operational current	AC-23A: 1600 A AC 50/60 Hz 220/240 V AC-23A: 1600 A AC 50/60 Hz 380/415 V AC-23A: 1600 A AC 50/60 Hz 440/480 V AC-23A: 1600 A AC 50/60 Hz 500/525 V AC-23A: 1600 A AC 50/60 Hz 660/690 V
[Ui] rated insulation voltage	800 V AC 50/60 Hz conforming to IEC 60947-3
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-3
[Ith] conventional free air thermal current	1600 A at 60 °C
[Icw] rated short-time withstand current	25 kA during 0.5 s conforming to IEC 60947-3 4 kA during 20 s conforming to IEC 60947-3

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Icm] rated short-circuit making capacity	52 kA 690 V AC at 50/60 Hz
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-3
Contact position indicator	Yes
Visible break	No
Mechanical durability	6000 cycles conforming to IEC 60947-3
Electrical durability	1000 cycles 440 V AC 50/60 Hz conforming to IEC 60947-3
Connection pitch	115 mm
Height	327 mm
Width	280 mm
Depth	147 mm
Net weight	18 kg

Environment

Standards	IEC 60947-3
Product certifications	ASEFA ASTA
Pollution degree	3 conforming to IEC 60947-3
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Packing Units

Package 1 Weight	15.866 kg
Package 1 Height	3.200 dm
Package 1 width	2.500 dm
Package 1 Length	3.000 dm

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------