



NEMA Control Relay, Type X, pneumatic timer attachment, one minute off delay, 10A resistive at 600VAC, 1NO and 1NC

8501XTD1



(!) Discontinued on: 4 Aug 2021

Main

Range Of Product	8501X
Relay Type	Control relay
Product Or Component Type	Timing relay

Complementary

Contacts Configuration	1 NO/1 NC	
Time Delay Type	Off-delay	
Time Range	0.260 s	
Electrical Connection	Screw clamp terminals	
Wire Gauge	AWG 18AWG 12 copper	
Terminal Tightening Torque	Control circuit: 1.021.36 N.m - on screw terminals	

Environment

Product Certifications	UL recognized E78403 CCN NKCR2
	CSA LR60905 class 3211 02

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	11.4 cm
Package 1 Length	16.3 cm
Package 1 Weight	344.7 g

Contractual warranty

Warranty	18 months
warranty	TO ITIOTILIS



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile