

# Product datasheet

Specifications



## PUSH BUTTON 600VAC 10A 30MM T-K

Local distributor code: 387227205 9001KR24RH6

### Main

Range of product	Harmony 9001K
Product or component type	Mushroom head push-button
Device short name	K
Type of operator	spring return
Operator profile	Red mushroom Ø 35 mm
Operator additional information	Screw-in with set screw security

### Complementary

Bezel material	Chromium plated metal
Mounting diameter	30 mm
Light source	without
Light source	Without
Light block supply	Without supply
Contacts type and composition	1 NC
Connections - terminals	Screw clamp terminals
Operating position	Any position
[Ie] rated operational current	10 A, AC-15 10 A, DC-13
Contact operation	Standard
Device presentation	Complete product

### Environment

Product certifications	NEMA UL listed file E42259 CCN NKCR CSA LR 25490 class 3211 03 CE
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	145.15 g

Package 1 Height	4.826 cm
Package 1 width	5.588 cm
Package 1 Length	9.398 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------