

# Product datasheet

Specifications



## Acti 9 -Auxiliary fault contact iSD - 1 C/O - AC/DC

Local distributor code: 396734925 A9A26927

### Main

Range of product	Acti 9
Product or component type	Fault contact
Device short name	ISD
Signal contacts composition	1 C/O
[In] rated current	1 A: 130 V DC 1.5 A: 60 V DC 2 A: 48 V DC 6 A: 24 V DC 3 A: 415 V AC - 50/60 Hz 6 A: 240 V AC - 50/60 Hz
9 mm pitches	1

### Complementary

Range compatibility	Acti9 iC60 Acti9 iC65 Acti9 iC60 RCBO Acti9 iID Acti 9 ARA Acti 9 RCA Acti 9 iDPN (China version) Acti9 iDPN Vigi Acti 9 iC40 Acti9 iSW-NA
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	4 kV
Local signalling	Mechanical indicator
Mounting mode	Clip-on
Mounting support	DIN rail
Height	86 mm
Width	9 mm
Depth	73 mm
Net weight	33 g
Colour	White
Connections - terminals	Screw clamp terminal2 cable(s) 2.5 mm <sup>2</sup> - rigid Screw clamp terminal2 cable(s) 1.5 mm <sup>2</sup> - flexible with ferrule Screw clamp terminal1 cable(s) 0.5...2.5 mm <sup>2</sup> - flexible Screw clamp terminal1 cable(s) 1...4 mm <sup>2</sup> - rigid
Wire stripping length	10 mm

Tightening torque	1 N.m
-------------------	-------

## Environment

Standards	EN/IEC 60947-5-1
IP degree of protection	IP20 conforming to EN/IEC 60947-5-1
Pollution degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	41.1 g
Package 1 Height	9.033 cm
Package 1 width	1.682 cm
Package 1 Length	7.46 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Weight	554.1 g
Package 2 Height	9.8 cm
Package 2 width	23.4 cm
Package 2 Length	8.4 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	120
Package 3 Weight	6 kg
Package 3 Height	26 cm
Package 3 width	28.3 cm
Package 3 Length	37.9 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

---

<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
-------------	---

---

**Contractual warranty**

---

<b>Warranty</b>	18 months
-----------------	-----------

---