Product datasheet

Specifications





Acti9 - RCA remote ctrl aux for iC60 3P-4P

Local distributor code: 402639147

A9C70114

EAN Code: 3606480097959

Main

Range Of Product	Acti9
Product Or Component Type	Remote control auxiliary
Device Short Name	RCA iC60
Signal Contacts Composition	1 OF volt-free contacts
Signalling Circuit Voltage	Volt-free contact 24230 V 0.011 A AC

Complementary

Complementary	
Control Type	Remote control impulse and maintained 230 V AC 50/60 Hz
Input Current	5 mA impulse 5 mA maintained
Impulse Duration	>= 200 ms control circuit
Response Time	< 500 ms
[Us] Rated Supply Voltage	230 V AC 50/60 Hz
Power Consumption In W	1 W
[Ui] Rated Insulation Voltage	400 V
[Uimp] Rated Impulse Withstand Voltage	6 KV
Value Of Setting	Mode A: reclosing authorized after tripping Mode B: reclosing inhibited after tripping Auto: remote control authorized Off: remote control inhibited
Local Signalling	Flashing green LED: ready to operate Flashing orange LED: not operational
Mounting Mode	Fixed
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	NO
9 Mm Pitches	7
Height	93 mm
Width	63 mm
Depth	75.5 mm
Net Weight	430 g
Colour	White
Electrical Durability	10000 cycles
Mechanical Durability	10000 cycles

Provision For Padlocking	Padlockable
Wire Stripping Length	Power supply: 10 mm for bottom connection Input: 10 mm for bottom connection Output: 8 mm for top connection
Tightening Torque	Auxiliary output: 0.7 N.m Auxiliary supply: 1 N.m Auxiliary input: 1 N.m
Range Compatibility	Acti 9 Acti9 iC60 Acti 9 Acti9 iC65 Acti 9 iMDU voltage adaptor
Product Compatibility	3P or 4P iC60 3P or 4P iC65 iMDU

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60947
Overvoltage Category	II
Tropicalisation	2
Relative Humidity	93 % at 40 °C
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-2560 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	11.000 cm
Package 1 Length	16.200 cm
Package 1 Weight	484.000 g
Unit Type Of Package 2	\$03
Number Of Units In Package 2	14
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	7.270 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information