Product datasheet

Specifications





iQuick PRD40r modular surge arrester - 1 pole + N - 350V - with remote transfer

Local distributor code: 397135358

A9L16292

EAN Code: 3606480387043

Main

Range Of Product	Acti9
Product Name	Acti9 iQuick PRD
Product Or Component Type	Surge arrester with pluggable cartridge
Device Short Name	iQuick PRD40r
Device Application	Distribution
Standards	EN 61643-11:2012 IEC 61643-11:2011
Product Certifications	CE
Quality Labels	KEMA-KEUR NF
Poles Description	1P + N
Remote Signalling	With
Signal Contacts Composition	1 SD (1 C/O)
Surge Arrester Type	Electrical distribution network
Earthing System	TN-S TT

Complementary

Surge Arrester Class Type	Type 2
Surge Arrester Technology	MOV + GDT
[Ue] Rated Operational Voltage	230 V AC (+/- 10 %) at 50/60 Hz
[In] Nominal Discharge Current	Common mode: 20 kA (L/PE) Common mode: 20 kA (N/PE) Differential mode: 20 kA (L/N)
[Imax] Maximum Discharge Current	Common mode: 40 kA L/PE Common mode: 40 kA N/PE Differential mode: 40 kA L/N
[Uc] Maximum Continuous Operating Voltage	Common mode: 264 V N/PE Common mode: 350 V L/PE Differential mode: 350 V L/N
Maximum [Up] Voltage Protection Level	Common mode <1.5 kV type 2 L/PE Common mode <1.5 kV type 2 N/PE Differential mode <2.5 kV type 2 L/N
Disconnector Device Type	Integrated circuit breaker - Icu 20 kA
Signalling Circuit Voltage	2 A/250 V AC 50/60 Hz
Mounting Mode	Clip-on (DIN rail)
9 Mm Pitches	8

Height	94 mm	
Width	72 mm	
Depth	75.9 mm	
Net Weight	0.44 kg	
Colour	White (RAL 9003)	
Connections - Terminals	Tunnel type terminal (upside) 2.535 mm ² Tunnel type terminal (downside) 2.525 mm ²	
Tightening Torque	2.5 N.m	

Environment

Ik Degree Of Protection	IK05 conforming to IEC 62262
Relative Humidity	595 %
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-2560 °C
Ambient Air Temperature For Storage	-4070 °C

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9 cm
Package 1 Width	8.7 cm
Package 1 Length	10 cm
Package 1 Weight	492 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	27
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	13.72 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Halogen Free Plastic Parts & Cables Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations