

# Product datasheet

Specifications



## Miniature circuit-breaker, Acti9 C120H, 2P, 100 A, C curve, 15000 A (IEC 60898-1), 15 kA (IEC 60947-2)

Local distributor code: 397539792 A9N18458

### Main

Range of product	C120
Range	Acti 9
Product name	C120
Product or component type	Miniature circuit-breaker
Device short name	C120H
Device application	Distribution
Poles description	2P
Number of protected poles	2
Neutral position	Left
[In] rated current	100 A at 30 °C
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	15000 A Icn at 230...400 V AC 50/60 Hz conforming to EN/IEC 60898-1 10 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA Icu at <= 250 V DC conforming to EN/IEC 60947-2 15 kA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 30 kA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2
Suitability for isolation	Yes conforming to IEC 60947-2

### Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	380...415 V AC 50/60 Hz 220...240 V AC 50/60 Hz 440 V AC 50/60 Hz <= 250 V DC 230...400 V AC 50/60 Hz
Magnetic tripping limit	5...10 x In
[Ics] rated service breaking capacity	7500 A 50 % conforming to EN/IEC 60898-1 - 230...400 V AC 50/60 Hz 5 kA 50 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 15 kA 50 % conforming to EN/IEC 60947-2 - 220...240 V AC 50/60 Hz 7.5 kA 50 % conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz 15 kA 100 % conforming to EN/IEC 60947-2 - <= 250 V DC
Limitation class	3 conforming to EN/IEC 60947-2
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to EN/IEC 60947-2

<b>[Uimp] rated impulse withstand voltage</b>	6 kV conforming to EN/IEC 60947-2
<b>Contact position indicator</b>	Yes
<b>Control type</b>	Toggle
<b>Local signalling</b>	ON/OFF indication
<b>Mounting mode</b>	Clip-on
<b>Mounting support</b>	35 mm symmetrical DIN rail
<b>Comb busbar and distribution block compatibility</b>	NO
<b>9 mm pitches</b>	6
<b>Height</b>	81 mm
<b>Width</b>	54 mm
<b>Depth</b>	73 mm
<b>Net weight</b>	0.41 kg
<b>Colour</b>	White
<b>Mechanical durability</b>	20000 cycles
<b>Electrical durability</b>	5000 cycles conforming to IEC 60947-2
<b>Connections - terminals</b>	Tunnel type terminals 1...50 mm <sup>2</sup> rigid Tunnel type terminals 1.5...35 mm <sup>2</sup> flexible
<b>Wire stripping length</b>	15 mm
<b>Tightening torque</b>	3.5 N.m
<b>Earth-leakage protection</b>	Separate block

## Environment

<b>Standards</b>	EN/IEC 60898-1 EN/IEC 60947-2
<b>Product certifications</b>	EAC
<b>IP degree of protection</b>	IP20 conforming to IEC 60529
<b>Pollution degree</b>	3 conforming to IEC 60947-2
<b>Overvoltage category</b>	IV
<b>Tropicalisation</b>	2 conforming to IEC 60068-1
<b>Relative humidity</b>	95 % at 55 °C
<b>Operating altitude</b>	2000 m
<b>Ambient air temperature for operation</b>	-30...60 °C
<b>Ambient air temperature for storage</b>	-40...70 °C

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Weight</b>	385 g
<b>Package 1 Height</b>	5.4 cm
<b>Package 1 width</b>	7.5 cm
<b>Package 1 Length</b>	8.5 cm
<b>Unit Type of Package 2</b>	S03

Number of Units in Package 2	36
Package 2 Weight	14.832 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	6
Package 3 Weight	2.378 kg
Package 3 Height	10 cm
Package 3 width	9 cm
Package 3 Length	33 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------