

# Product datasheet

Specifications



## Acti9 iID - RCCB - 4P - 80A - 300mA - type A

TSI Code: 399366992 A9R24480

### Main

Range	Acti 9
Product name	Acti9 iID
Product or component type	Residual current circuit breaker (RCCB)
Device short name	iID
Poles description	4P
Neutral position	Left
[In] rated current	80 A
Network type	AC
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type A

### Complementary

Device location in system	Outgoer
Network frequency	50/60 Hz
[Ue] rated operational voltage	380...415 V AC 50/60 Hz
Residual current tripping technology	Voltage independent
Rated breaking and making capacity	Idm 1500 A Im 1500 A
Rated conditional short-circuit current	10 kA
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
Contact position indicator	Yes
Control type	Toggle
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8

Height	91 mm
Width	72 mm
Depth	73.5 mm
Product weight	0.37 kg
Colour	White
Mechanical durability	20000 cycles
Electrical durability	AC-1: 10000 cycles
Locking options description	Padlocking device
Connections - terminals	Single terminal top or bottom 1...35 mm <sup>2</sup> rigid Single terminal top or bottom 1...25 mm <sup>2</sup> flexible Single terminal top or bottom 1...25 mm <sup>2</sup> flexible with ferrule
Wire stripping length	14 mm for top or bottom connection
Tightening torque	3.5 N.m top or bottom

## Environment

Standards	EN/IEC 61008-1
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to EN/IEC 61008-1
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	353 g
Package 1 Height	7.7 cm
Package 1 width	8.5 cm
Package 1 Length	9.6 cm
Unit Type of Package 2	S03
Number of Units in Package 2	27
Package 2 Weight	10.166 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>

Product out of China RoHS scope. Substance declaration for your information

---

<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
<b>Halogen content performance</b>	Halogen free plastic parts product

---

**Contractual warranty**

---

<b>Warranty</b>	18 months
-----------------	-----------

---