



Main

Range	Acti 9
Product or component type	Add-on residual current devices
Device short name	Vigi iC60
Poles description	1P + N
Neutral position	Left
[In] rated current	63 A
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Instantaneous
Earth leakage protection type	Type A
Network type	AC
Network frequency	50/60 Hz
[Ue] rated operational voltage	240 V AC 50/60 Hz conforming to IEC 61009-1
Standards	EN 61009-1 IEC 61009-1
9 mm pitches	4

Complementary

Device location in system	Outgoer
Residual current tripping technology	Voltage independent
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-2
Range compatibility	Acti 9 iC60
Product compatibility	Single terminal
Local signalling	Trip indicator
Mounting mode	Clip-on
Mounting support	DIN rail

Electrical connection to mcb	By screws
Comb busbar and distribution block compatibility	Bottom: YES
Height	91 mm
Width	54 mm
Depth	73.5 mm
Net weight	0.165 kg
Connections - terminals	Tunnel type terminal downside for 1 cable(s) 1...35 mm ² rigid without cable end Tunnel type terminal downside for 1 cable(s) 1...25 mm ² flexible without cable end Tunnel type terminal downside for 1 cable(s) 1...25 mm ² flexible with cable end
Wire stripping length	14 mm for bottom connection
Tightening torque	3.5 N.m bottom

Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3 conforming to IEC 60947-2
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to IEC 61009-1
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	213 g
Package 1 Height	8.5 cm
Package 1 width	11.3 cm
Package 1 Length	14.5 cm
Unit Type of Package 2	S03
Number of Units in Package 2	15
Package 2 Weight	3.682 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------