

# Product datasheet

Specifications



pre-wired connector - cable 5 m - for passive splitter box - with 8 channels

Local distributor code: 402704124 ABE9XCA1805

## Main

|                                       |                          |
|---------------------------------------|--------------------------|
| Range of product                      | Advantys ABE9            |
| Accessory / separate part category    | Connection accessories   |
| Accessory / separate part designation | Pre-wired connector      |
| Number of channels                    | 8                        |
| Product destination                   | ABE9C1280M<br>ABE9C1281M |
| Cable length                          | 5 m                      |

## Complementary

|            |         |
|------------|---------|
| Net weight | 1.51 kg |
|------------|---------|

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Weight             | 1.158 kg |
| Package 1 Height             | 5 cm     |
| Package 1 width              | 27 cm    |
| Package 1 Length             | 28 cm    |
| Unit Type of Package 2       | S03      |
| Number of Units in Package 2 | 6        |
| Package 2 Weight             | 7.508 kg |
| Package 2 Height             | 30 cm    |
| Package 2 width              | 30 cm    |
| Package 2 Length             | 40 cm    |

## Offer Sustainability

|                    |   |
|--------------------|---|
| REACH Regulation   | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC | Yes   |
| EU RoHS Directive  | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |

---

|                                   |  |
|-----------------------------------|--|
| <b>Toxic heavy metal free</b>     | Yes                                    |
| <b>Mercury free</b>               | Yes                                    |
| <b>RoHS exemption information</b> | <a href="#">Yes</a>                    |
| <b>China RoHS Regulation</b>      | <a href="#">China RoHS declaration</a> |

---

### **Contractual warranty**

---

|                 |           |
|-----------------|-----------|
| <b>Warranty</b> | 18 months |
|-----------------|-----------|

---