

Product datasheet

Specifications



connecting cable - Advantys Telefast - 3m - 32 O 100 mA - for Allen Bradley

TSI Code: 402704357 ABFH40H301

! To be discontinued on: 31 March 2022

! To be end-of-service on: 31 March 2022

! To be discontinued

Main

Accessory / separate part destination	Allen Bradley PLC
Range of product	Advantys Telefast
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connection cable
Accessory / separate part designation	Connecting cable
Number of channels	16

Complementary

Product compatibility	SLC500
Cable length	3 m
Type of signal	100 mA 32 channel output
Electrical connection	1 connector HE10, 40 ways for PLC side 2 connectors HE10, 20 ways for Telefast end
AWG gauge	AWG 22
Wire section	0.324 mm ²

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	909 g
Package 1 Height	4.5 cm
Package 1 width	24 cm
Package 1 Length	24 cm
Unit Type of Package 2	S02
Number of Units in Package 2	6
Package 2 Weight	5.84 kg
Package 2 Height	15 cm

Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------