

Product datasheet

Specifications



plug-in solid state relay- 12.5 mm - input -24 V AC

ABS7EA3B5

Main

Range of product	Advantys Telefast ABE7
Product or component type	Plug-in solid state relay
Relay type	Input relay
Minimum ordered quantity	Set of 4

Complementary

Response time	<= 20 ms from state 0 to 1 <= 20 ms from state 1 to 0
Width pitch dimension	12 mm
Product compatibility	ABE7P16F310 ABE7P16F310E ABE7P16F312
Discrete input voltage	24 V AC 50 Hz
Discrete output voltage	5...24 V DC
Product weight	0.014 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	11 g
Package 1 Height	5 cm
Package 1 width	5.1 cm
Package 1 Length	6.5 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	4
Package 2 Weight	46 g
Package 2 Height	5 cm
Package 2 width	5.1 cm
Package 2 Length	6.5 cm
Unit Type of Package 3	S01
Number of Units in Package 3	64

Package 3 Weight	961 g
Package 3 Height	15 cm
Package 3 width	15 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------