



## Main

Range of product	Advantys Telefast ABE7
Product or component type	Plug-in solid state relay
Relay type	Input relay
Minimum ordered quantity	Set of 4

## Complementary

Response time	<= 0.05 ms from state 0 to 1 <= 0.4 ms from state 1 to 0
Width pitch dimension	12 mm
Product compatibility	ABE7P16F310E ABE7P16F312 ABE7P16F310
Discrete input voltage	48 V DC, type 2
Discrete output voltage	5...24 V DC
Product weight	0.014 kg

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	11 g
Package 1 Height	5 cm
Package 1 width	5.2 cm
Package 1 Length	6.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Weight	45 g
Package 2 Height	5 cm

Package 2 width	5.2 cm
Package 2 Length	6.5 cm
Unit Type of Package 3	S01
Number of Units in Package 3	64
Package 3 Weight	948 g
Package 3 Height	15 cm
Package 3 width	15 cm
Package 3 Length	40 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

### Contractual warranty

Warranty	18 months
----------	-----------

---

## Internal Wiring Diagram

---

