

# Product datasheet

Specifications



## C60HB 2P 4A B BSEN

C60HB204

⚠ Discontinued on: 31 Mar 2017

⚠ Discontinued

### Main

|                           |                           |
|---------------------------|---------------------------|
| Device Application        | Distribution              |
| Range                     | Multi9                    |
| Product Name              | C60                       |
| Product Or Component Type | Miniature circuit-breaker |
| Device Short Name         | C60H                      |
| Poles Description         | 2P                        |
| Number Of Protected Poles | 2                         |
| Trip Unit Technology      | Thermal-magnetic          |
| Curve Code                | B                         |

### Complementary

|                    |                                                                                                                                                                                                                                                                                                                                                                                                                             |
|--------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [In] Rated Current | 4 A                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Breaking Capacity  | 10 kA Icn at 230/400 V AC 50/60 Hz conforming to EN 60898<br>10 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2<br>15 kA Icu at 400...415 V AC 50/60 Hz conforming to IEC 60947-2<br>25 kA Icu at 125 V DC 2P conforming to IEC 60947-2<br>30 kA Icu at 230...240 V AC 50/60 Hz conforming to IEC 60947-2<br>40 kA Icu at 125 V DC 3P conforming to IEC 60947-2<br>50 kA Icu at 250 V DC 4P conforming to IEC 60947-2 |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications