

Product datasheet

Specifications



C60HB 2P 20A B BSEN

C60HB220

 **Discontinued on:** 31 Mar 2017

 **Discontinued**

Main

Device Application	Distribution
Range	Multi9
Product Name	C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60H
Poles Description	2P
Number Of Protected Poles	2
Trip Unit Technology	Thermal-magnetic
Curve Code	B

Complementary

[In] Rated Current	20 A
Breaking Capacity	10 kA Icn at 230/400 V AC 50/60 Hz conforming to EN 60898 10 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 15 kA Icu at 400...415 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 125 V DC 2P conforming to IEC 60947-2 30 kA Icu at 230...240 V AC 50/60 Hz conforming to IEC 60947-2 40 kA Icu at 125 V DC 3P conforming to IEC 60947-2 50 kA Icu at 250 V DC 4P conforming to IEC 60947-2

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications