Product datasheet

Specification





Acti9 - MINt - silent electronic timer - adjustable from 0.5 to 60 minutes

Local distributor code: 399370470

99370470 CCT15234

EAN Code: 3303431062645

Main

| Range Of Product | Acti9 |
|---------------------------|---|
| Product Name | Acti9 MIN |
| Device Short Name | MINt |
| Product Or Component Type | Silent electronic timer |
| Product Compatibility | Mechanical compatibility with electrical comb busbars |
| Function Available | Impulse relay Switch-off warning |
| Colour Tint | White (RAL 9003) |

Complementary

| Device Application | Building |
|--------------------------------|--|
| Load Type | Fluorescent lamp 22 x electronic ballast 1500 VA Fluorescent lamp 22 x electronic ballast 23 W 230 V AC halogen lamp 3600 W 230 V AC incandescent lamp 3600 W Fluorescent lamp 24 x electronic ballast 15 W Fluorescent lamp 27 x electronic ballast 11 W Fluorescent lamp 34 x electronic ballast 7 W Dual mounted fluorescent tubeconventional ballast 3600 VA Fluorescent tubeelectronic ballast 1000 VA Non-corrected fluorescent tubeconventional ballast 3600 VA Parallel-corrected fluorescent tubeconventional ballast 3600 VA Serial-corrected fluorescent tubeconventional ballast 3600 VA |
| Power Consumption In Va | 6 VA |
| Maximum Switching Current | 16 A - 230 V AC pf = 1 |
| [Ue] Rated Operational Voltage | 230 V AC +10 % -15 % at 50/60 Hz |
| Time Delay | Adjustable from 0.5 to 20 minutes |
| Mounting Support | DIN rail |
| 9 Mm Pitches | 2 |
| Connections - Terminals | Screw terminals - <= 6 mm² |
| Electrical Insulation Class | Class II |
| Width | 18 mm |
| Height | 89 mm |
| Depth | 66 mm |
| Net Weight | 76 g |

Environment



| Ambient Air Temperature For Operation | -2550 °C |
|---------------------------------------|----------|
| Ip Degree Of Protection | IP20 B |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 7.2 cm |
| Package 1 Width | 2.2 cm |
| Package 1 Length | 10.5 cm |
| Package 1 Weight | 101 g |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 130 |
| Package 2 Height | 30 cm |
| Package 2 Width | 30 cm |
| Package 2 Length | 40 cm |
| Package 2 Weight | 13.604 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |