



13A 250V Surface Mount Single Gang Socket Outlet IP56

CSO313

! Discontinued on: 2 Aug 2021

EAN Code: 9311554288143

! To be discontinued

Main

Range	Kavacha
Product Or Component Type	Socket-outlet
Device Short Name	AS

Complementary

Wiring Device Mounting	Surface
Rated Current	13 A at 250 V AC
Width	80 mm
Height	117 mm
Depth	80 mm

Environment

Ip Degree Of Protection	IP56
Standards	IEC 60529 BS 1363-2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.800 cm
Package 1 Width	8.600 cm
Package 1 Length	12.500 cm
Package 1 Weight	290.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	44
Package 2 Height	27.500 cm
Package 2 Width	36.000 cm
Package 2 Length	45.500 cm
Package 2 Weight	13.398 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	792

Package 3 Height	115.000 cm	
Package 3 Width	120.000 cm	
Package 3 Length	100.000 cm	
Package 3 Weight	241.164 kg	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations