

# Product datasheet

Specifications



## Ultimate Screwless flat plate - switched socket - 2 gangs - stainless steel

GU3421BSS

⚠ Discontinued on: 1 Jan 2006

⚠ Discontinued

### Main

Aesthetic Name	Screwless flat plate
Product Or Component Type	Switched socket
Rated Current	13 A at 230 V AC 50 Hz
Fixing Mode	By screws M3.5 x 30 mm
Colour Tint	Stainless steel

### Complementary

Device Presentation	Complete product
Outlet Poles Configuration	1P
Outlet Standard Description	3 pins
Outlet Standard Deviation	British
Actuator	Rocker
Number Of Gangs	2 gangs
Earth Circuit	Standard earth
Pilot Light	Neon indicator
Device Mounting	Wall mounted
Connections - Terminals	Screw terminal
Material	Steel
Quantity Per Set	Set of 1
Height	88 mm
Width	148 mm
Depth	30 mm

### Environment

Ip Degree Of Protection	IP20
Standards	BS 1363

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	4.2 cm
Package 1 Length	16.2 cm
Package 1 Weight	291 g

## Contractual warranty

Warranty	18 months
----------	-----------