

Product datasheet

Specifications



Ultimate - blank plate - 1 gang - polished chrome

Local distributor code:

391288382

GU8510PC

EAN Code: 5018486532033

Main

Range	Ultimate
Aesthetic Name	Low profile
Product Or Component Type	Blank plate
Colour Tint	Chrome

Complementary

Range Compatibility	Ultimate Ultimate Low Profile
Device Mounting	Wall mounted
Fixing Mode	By screws
Number Of Gangs	1 gang
Surface Finish	Polished
Material	Steel
Height	88 mm
Width	88 mm
Depth	15 mm
Net Weight	0.091 kg

Environment

Standards	BS 5733
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	9.500 cm
Package 1 Length	9.500 cm
Package 1 Weight	119.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	21.500 cm
Package 2 Width	42.500 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	50.000 cm
Package 2 Weight	12.660 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1600
Package 3 Height	102.500 cm
Package 3 Width	120.000 cm
Package 3 Length	100.000 cm
Package 3 Weight	222.560 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability


Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration