Product datasheet

Specifications





Galaxy VS Battery Breaker Box 20-80kW 400V

GVSBBB20K80H

Overview

Presentation	Wall mounted battery breaker box for use with third party battery solutions.
Lead Time	Usually Ships within 2 Weeks
Main	
Battery Type	VRLA
Physical	
Colour	White
Height	65 cm
Width	50 cm
Depth	28 cm
Net Weight	25 kg

Environmental

Ambient Air Temperature For Operation	040 °C
Ambient Air Temperature For Storage	-2555 °C

Packing Units

<u>~</u>	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	48 cm
Package 1 Width	84 cm
Package 1 Length	122 cm
Package 1 Weight	45 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information