# **Product datasheet**

Specifications





# Galaxy VS Maintenance Bypass Panel, single unit, 10-20kW 400V wallmount

Local distributor code: 422503774

GVSBPSU10K20H

### **Overview**

Presentation	Maintenance bypass panel for complete isolation of the UPS during service operations.
Lead Time	Usually Ships within 2 Weeks

# **Physical**

Colour	White	
Height	45 cm	
Width	40 cm	
Depth	15 cm	
Net Weight	12 kg	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	26 cm
Package 1 Width	53 cm
Package 1 Length	59 cm
Package 1 Weight	20 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	6
Package 2 Height	94 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	132 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >









Energy Efficient Take-back Transparency RoHS/REACh

### Resource performance

Energy Efficient Product

✓ Take-Back Program Available

## Well-being performance

Mercury Free

Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

China RoHS declaration

Environmental Disclosure

Product Environmental Profile

Circularity Profile

End of Life Information