Product datasheet





integrated servo motor - 2.2 Nm -6000 rpm - keyed shaft - with brake

ILM0703P11F0000

! Discontinued on: 9 Feb 2023

① Discontinued

EAN Code: 3606485293967

Main

| Range Of Product | PacDrive 3 |
|---------------------------|------------------------------|
| Product Or Component Type | Servo motor integrated drive |
| Device Short Name | ILM |

Complementary

| [Us] Rated Supply Voltage | 250700 V |
|---------------------------|---|
| Continuous Stall Current | 3 A |
| Continuous Stall Torque | 2.2 N.m |
| Peak Stall Torque | 8.7 N.m |
| Nominal Output Power | 720 W |
| Nominal Torque | 1.15 N.m |
| Nominal Speed | 6000 rpm |
| Maximum Current Irms | 12 A |
| [In] Rated Current | 1.5 A |
| Shaft End | Keyed |
| Second Shaft | Without second shaft end |
| Shaft Diameter | 14 mm |
| Shaft Length | 30 mm |
| Key Width | 20 mm |
| Feedback Type | Absolute single turn SinCos Hiperface |
| Speed Feedback Resolution | 128 periods |
| Holding Brake | With |
| Holding Torque | 3 N.m holding brake |
| Mounting Support | International standard flange |
| Motor Flange Size | 70 mm |
| Torque Constant | 0.76 N.m/A at 120 °C |
| Back Emf Constant | 49 V/krpm at 20 °C |
| Number Of Motor Poles | 6 |
| Rotor Inertia | 0.88 kg.cm² |
| Stator Resistance | 2.7 Ohm at 20 °C for Ph/Ph 1.88 Ohm at 120 °C for Ph/N |

| Stator Inductance | 13 mH at 20 °C for Ph/Ph |
|---------------------------------------|---------------------------|
| | 6.5 mH at 120 °C for Ph/N |
| Maximum Radial Force Fr | 730 N at 1000 rpm |
| | 580 N at 2000 rpm |
| | 510 N at 3000 rpm |
| | 460 N at 4000 rpm |
| | 430 N at 5000 rpm |
| | 400 N at 6000 rpm |
| Maximum Axial Force Fa | 0.2 x Fr |
| Type Of Cooling | Natural convection |
| Length | 293 mm |
| Number Of Motor Stacks | 3 |
| Centring Collar Diameter | 60 mm |
| Centring Collar Depth | 2.5 mm |
| Number Of Mounting Holes | 4 |
| Mounting Holes Diameter | 5.5 mm |
| Circle Diameter Of The Mounting Holes | 82 mm |
| Net Weight | 4.7 kg |

Environment

Ip Degree Of Protection IP54

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 26.0 cm |
| Package 1 Width | 20.0 cm |
| Package 1 Length | 59.0 cm |
| Package 1 Weight | 5.2 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| | Reach Free Of Svhc |
|----------|--------------------------------|
| ② | Mercury Free |
| | Rohs Exemption Information Yes |
| ② | Pvc Free |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |