



Thorsman Mini 1,5W LED rechargeable handheld work light (with usb cable)

IMT33093

! Discontinued on: 27 Jul 2021

! Discontinued

EAN Code: 3606485418551

Main

Range	Thorsman
Product Name	Thorsman Mini 1.5 LED
Product Or Component Type	Handheld work lamp
Light Source	COB LED 1.5 W

Complementary

Type Of Installation	Indoor
[Ue] Rated Operational Voltage	5 V
Network Type	AC
Network Frequency	50/60 Hz
Output Voltage	5 V DC, 1 A
Bulb Lifespan	50000 h
Colour Rendering Index	R _a =70
Illuminance	0.5 m: 80 lux
Provided Equipment	USB cable
Height	120 mm
Width	59 mm
Depth	25 mm
Net Weight	112 g

Environment

Environmental Characteristic	Dustproof
Ip Degree Of Protection	IP65
Quality Labels	CE
Ambient Air Temperature For Operation	-1040 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm

Package 1 Width	6.8 cm
Package 1 Length	16.2 cm
Package 1 Weight	170 a

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations