Product datasheet

Specification





Straight length, Canalis KBA, 25 A, 1 circuit 3L+N+PE, 2 tap-off units, 3 m, white

Local distributor code: 395945113

KBA25ED4302W

EAN Code: 3606480498763

Main

Range Of Product	Canalis	
Device Short Name	КВА	
Offer Type	Classic Control system	
Product Or Component Type	Straight length	
Busbar Description	tion Distribution length	
Device Application	Lighting Power socket distribution	
[le] Rated Operational Current	25 A at 35 °C	
[Ue] Rated Operational Voltage	230400 V	
Network Frequency	Frequency 50/60 Hz	
Busbar Trunking Polarity	3L + N + PE	
Number Of Circuits	er Of Circuits 1	
Number Of Tap-Off Outlets	2	
Control Type	Communicating	
Communication Port Protocol	ation Port Protocol DALI	
Mounting Mode	By clips	

Complementary

[Uimp] Rated Impulse Withstand Voltage	4 kV
[Ui] Rated Insulation Voltage	690 V
[Icw] Rated Short-Time Withstand Current	0.44 kA
[lpk] Rated Peak Withstand Current	4.4 kA
Thermal Stress Limit	195 kA².s
Maximum Radiated Magnetic Field	2 pT
Thdi	015 % 25 A 1533 % 20 A 33100 % 16 A
Maximum Voltage Drop	<0.72 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.67 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.61 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.54 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Standards	EN/IEC 61439-6 EN/IEC 61439-1
Width	30 mm

Height	46 mm
Length	3 m
Colour	White (RAL 9003)
Net Weight	2.4 ka

Environment

Ip Degree Of Protection	IP55 conforming to EN/IEC 60529
Ik Degree Of Protection	IK06 conforming to EN/IEC 62262
Ambient Air Temperature For Operation	035 °C (100 % of In) 3540 °C (96 % of In) 4045 °C (93 % of In) 4550 °C (89 % of In) 5055 °C (85 % of In)

Packing Units

PCE
1
4.6 cm
3.2 cm
314 cm
3 kg
BB1
6
10.5 cm
10.5 cm
318.5 cm
18 kg
PAL
144
53 cm
64 cm
320 cm
452 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Product datasheet

KBA25ED4302W

Dimension Drawings

