Product datasheet

Specification





Multi-fixing LED lamp without socket - 230 V AC - 10W

NSYLAMLD

EAN Code: 3606481203083

Main

| Range Of Product | Lighting and power sockets | |
|---------------------------------------|-----------------------------|--|
| Accessory / Separate Part Category | Lighting accessory | |
| Product Or Component Type | Lamp | |
| Device Application | Multi-purpose | |
| Device Composition | 1 lamp 1 fixing elements | |
| Power Factor | 0.9 | |

Complementary

| Outlet Standard | Without socket |
|--------------------------------|---|
| Rated Lamp Wattage | 10 W |
| [Ue] Rated Operational Voltage | 120/230 V AC 50/60 Hz |
| Bulb Base | Integral LED |
| Bulb Type | LED |
| Control Type | Built-it switch |
| Luminous Flux | 950 lm |
| Colour Temperature | 4000 K |
| Service Life In Hours | 25000 h |
| Electrical Connection | Cable quick connector 3 m not supplied Cable quick connector 1 m not supplied |
| Mounting Support | Bracket DIN rail Metal parts |
| Fixing Mode | Magnetic fixing Screws Clip-in |
| Range Compatibility | Spacial Thalassa |
| Material | PC (UL94 V-0) |
| Length | 372 mm |
| Height | 63 mm |
| Width | 40 mm |
| Colour | Black (RAL 9005) |

Environment

| Ip Degree Of Protection | IP20 conforming to IEC 60529 |
|---------------------------------------|--|
| Electrical Insulation Class | Class II |
| Electromagnetic Compatibility | EMC immunity conforming to EN 55015 |
| Standards | UL 8750 UL 94 IEC 60598 UL 1598 UL 508 A EN 55015 |
| Ambient Air Temperature For Operation | -1665 °C |
| Ambient Air Temperature For Storage | -1060 °C |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.500 cm |
| Package 1 Width | 8.000 cm |
| Package 1 Length | 40.000 cm |
| Package 1 Weight | 769.800 g |
| Unit Type Of Package 2 | S04 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 30.000 cm |
| Package 2 Width | 40.000 cm |
| Package 2 Length | 60.000 cm |
| Package 2 Weight | 8.459 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| 9 | Toxic Heavy Metal Free | |
| ② | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |