Product datasheet





wall-mounting encl. polyester monobloc IP66 H308xW255xD160mm+bakelite mount.pl.

Local distributor code:

403422971 NSYPLM3025BG

EAN Code: 3606480776441

Main

Range	Thalassa
Product Name	Thalassa PLM
Device Short Name	PLM
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	308 mm
Nominal Width	255 mm
Nominal Depth	160 mm
Enclosure Mounting	Wall mounted
Device Composition	1 body 1 door 1 mounting plate 1 lock
Door Type	Plain
Lock Type	3 mm double-bar lock

Complementary

Number Of Locks	1
Mounting Plate Description	Plain bakelite
Accessibility For Operation	Front
Removable Parts	Door by hinges Mounting plate by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	NEMA classification 13 NEMA classification 4X IEC 62208
Product Certifications	UL
Electrical Insulation Class	Class II

Environment

Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Fire Resistance	960 °C conforming to IEC 62208

Ambient Air Temperature For -40...80 °C
Operation

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.500 cm
Package 1 Width	26.500 cm
Package 1 Length	32.500 cm
Package 1 Weight	3.461 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	15
Package 2 Height	45.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	63.915 kg

Logistical informations

Country Of Origin

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations